



SA10RA Performance Curves



Max Sizeable RPM = 1800 RPM. Curve shown extended beyond this point for reference only.



Notes:
 The static pressure of non-woven polyester filters is 2 times the static pressure of standard EZ Klean Filters.
 The static pressure of throw-away filters is 1.33 times the static pressure of standard EZ Klean Filters.
 The static pressure of throw-away MERV 13 filters is 1.9 times the static pressure of standard EZ Klean Filters.
 Throw-away filters are used in v-bank intakes only.

