



SA10RAD Performance Curves



Max Sizeable RPM = 1075 RPM. Curve shown extended beyond this point for reference only.

- Motor BMN48-750I2-50-230/277 has an rpm range of 300 to 1075.
- Motor BMN48-750I2-60-230/277 has an rpm range of 300 to 1075.
- Motor M055PWCUK0315-ECM-50-115 has an rpm range of 300 to 1075.
- Motor M055PWCUK0315-ECM-50-230 has an rpm range of 300 to 1075.
- Motor M055PWCUK0315-ECM-60-115 has an rpm range of 300 to 1075.
- Motor M055PWCUK0315-ECM-60-230 has an rpm range of 300 to 1075.



Notes:

- The static pressure of non-woven polyester filters is 2 times the static pressure of standard EZ Klean Filters.
- The static pressure of throw-away filters is 1.33 times the static pressure of standard EZ Klean Filters.
- The static pressure of throw-away MERV 13 filters is 1.9 times the static pressure of standard EZ Klean Filters.
- Throw-away filters are used in v-bank intakes only.

