
## RARTU3-E.304-20 Performance Curve



## Max Sizeable RPM = 1800 RPM. Curve shown extended beyond this point for reference only.

Motor DHP00545 has an rpm range of 900 to 1750.

Motor DHP0056 has an rpm range of 900 to 1165.

Motor DHP7/545 has an rpm range of 900 to 1750.

Motor DTP0054 has an rpm range of 900 to 1750.

Motor DTP0054-50 has an rpm range of 900 to 1435.

Motor DTP0056 has an rpm range of 900 to 1150.

Motor DTP7/54 has an rpm range of 900 to 1750.

Motor DTP7/54-50 has an rpm range of 900 to 1470.

Motor EP00545 has an rpm range of 900 to 1745.

Motor EP7/545 has an rpm range of 900 to 1755.

Motor GP0054 has an rpm range of 900 to 1800.

Motor GP0054-50 has an rpm range of 900 to 1440.

Motor GP7/54 has an rpm range of 900 to 1800.

Motor GP7/54-50 has an rpm range of 900 to 1440.